



# FASSON Compatibility Matrix

<b>FASSON® FILM FACESTOCK</b>	<b>Wax</b>	<b>W-R</b>	<b>Resin</b>	<b>Blue-Edge</b>
<b>Coated Paper:</b>				
Trans-Therm® 1C	S2	L3, S3		HT5 W-R
Trans-Therm® 2C	S2	L3, S3		HT5 W-R
Trans-Therm® C	S2	L3, S3		HT5 W-R
<b>Uncoated Paper:</b>				
Trans-Therm® 2	S2	L3		HT5 W-R
<b>Glossy Paper:</b>				
TransGloss™	S2	L3, S3		HT5 W-R
<b>Topcoated Polyester:</b>				
1M & 2M White Polyester TC			HL21, HL30, HL32, HL45	
1M & 2M Clear Polyester TC			HL21, HL30, HL32, HL45	
1M & 2M Bright Chrome Polyester TC			HL21, HL30, HL32, HL45	
1M & 2M Brushed Chrome Polyester TC			HL21, HL30, HL32, HL45	
1M & 2M Matte Chrome Polyester TC			HL21, HL30, HL32, HL45	
<b>Matte Topcoated Polyester:</b>				
2M Matte White TC PET			HL21, NK21, HL32, HL45	
2M CopyCode White PET			HL21, NK21, HL32, HL45	
2M CopyCode II White PET			HL21, NK21, HL32, HL45	
2M CopyCode Chrome PET			HL21, NK21, HL32, HL45	
2M CopyCode II Chrome PET			HL21, NK21, HL32, HL45	
<b>Print-Treated Polyester:</b>				
1M & 2M White Printable Polyester			HL21, HL30, HL32, HL45	
1M & 2M Clear Printable Polyester			HL21, HL30, HL32, HL45	
2M Platinum Printable Polyester			HL21, HL30, HL32, HL45	



# FASSON Compatibility Matrix Cont.

## FASSON® FILM FACESTOCK

## Wax Wax-Resin Resin

## Near-Edge

### Overlaminates:

1M & 2M Super Cold™ Seal  
1M & 2M Performance PET

HL21, HL30, HL32, HL45  
HL21, HL30, HL32, HL45

### Biaxially Oriented Polypropylene:

3M Matte White BOPP  
2M BOPP TC

S2 L3, S3  
S2 L3, S3

HL21, HL30, HL32, HL45 HT8+ W-R  
HL21, HL30, HL32, HL45 HT8+ W-R

### Synthetic Paper:

3M Matte White S.P. TC  
Smudge Proof Kimdura®

S2 L3, S3  
S2 L3, S3

HL21, HL30, HL32, HL45  
HL21, HL30, HL32, HL45

1. The following Fasson® substrates have been tested and approved for use with Dynic USA Corporation thermal transfer ribbons.
2. Dynic USA Corporation recommends that the ribbon be tested independently to match specific label requirements, and in order to determine optimum print conditions.
3. Fasson® is a registered trademark of Avery Dennison.



Fasson Roll North America



7670 Auburn Road  
Painesville, OH 44077  
Phone: 440-358-4867 or 800-944-8511  
Fax: 440-358-4712  
[www.fasson.com](http://www.fasson.com) or [www.averydennison.com](http://www.averydennison.com)

**Headquarters:**  
4750 N.E. Dawson Creek Drive  
Hillsboro, OR 97124  
Phone: (503) 693-1070 Fax: (503) 648-1185  
<http://www.dynic.com>